

GemiClean SW

Screen Washing machine

TYPICAL FEATURES

- Rotary screen dimensions: Repeats 537, 640 and 914 mm. Length up to 1.500 mm. Note: Upon request also available for other screen dimensions.
- Screen position: Executed with 1 or 2 vertical washing cabinets:
 - Type SW-1: 1 washing cabinet.
 - Type SW-2: 2 washing cabinets, cleaning of 1 screen at a time.
 - Type SW-2/2: 2 washing cabinets, cleaning of 2 screens simultaneously.
- Fixation of the screen top and bottom: Open cone body. (3-pinpoint fixation system).



- Cleaning of inside and outside with spray nozzle system with no moving parts in the contaminated area.
- Cleaning liquid: Water or solvent.
- Cleaning-/drying cycle: Top - bottom. Cycles free adjustable.
- Sliding door with release of washing process and exhaust air system.
- Washing cabinet provided with connection to exhaust air system. Optional available with separation filter and exhaust ventilator.
- Optional with sedimentation system.
- Optional in ATEX Zone II 3G execution.